

1050

O DEFINO

CE

# THE WINNING COMBINATION

Double sealing mixproof valve with leak detection, without elastomer seal







Based on the generation of DCX3 valves, the NEOS double seal mixproof valve, with leak detection and without elastomer seal, combines various technologies for a unique result meeting market requirements in terms of cleanability, durability and sanitary applicability.

Benefiting from patented technology and meeting the recommendations of the EHEDG, the NEOS valve is, by design, particularly suitable for CIP "Cleaning In Place" applications by excluding the use of elastomer seals in contact with the process fluid.

It is an economically attractive alternative to double seat valves, as it offers a sufficient level of protection for product lines before pasteurisation and utility networks (CIP - water flush) while standing up to frequent cleaning and the use of aggressive products.

It is able to report the failure of a sealing point owing to its leaking chamber, thereby preventing any risk of mixing between lines.

Built into a manifold, the crossbody version allows scraping of the lower lines.

Available from  $\emptyset$  25, it is fitted as standard with a PTFE diaphragm providing a physical barrier between the inside of the valve and the external environment.

Its design with a limited number of seals simplifies servicing operations, thereby reducing maintenance times and costs.

As standard the valve is equipped with a "normally open"

(NO) leak indicator. An optional microvalve can be added

Each of these microvalves can be controlled separately using

an ACS control unit equipped with 2 or 3 solenoid valves,

Leak indicator and cleaning microvalve featuring a new design:

to clean the leak chamber, with the valve closed.

# **3 SPECIALLY DESIGNED COMPONENTS**

TO BETTER MEET USER REQUIREMENTS

# PFA FLOATING SEAL

With an original profile, it features two sealing points on and below the valve plug. The floating seal principle offers the valve excellent cleanability. The openings promote the flow of fluid on either side of the floating seal.

The PFA seal's plastomer structure guarantees the absence of porosity or cracking, thereby eliminating the risk of contamination and bacterial growth. It has excellent resistance to particularly aggressive chemicals and high temperatures.



SINGLE PIECE PLUG Hygienic plug design; single piece without threads or welds.





PFA seal

LEAK INDICATOR

▶ 1/8 gas connection

depending on the configuration.

Return spring outside the leak chamber, not in contact with the process fluid

# ACS LED control unit

- > View valve status from a distance
- > Easily configurable and removable
- > Resin-coated electronic module
- > Equipped with 1 or 2 proximity sensors > Equipped with 2 or 3 solenoid valves, depending on the configuration
- > Available in point-to-point or AS-i version > To avoid micro-leaks when the valve is
- operated, we recommend separating main actuator control from that of the micro-valves.

By default, the valves are proposed fitted with a:

> 2 SV ACS unit for NEOS with 1 indicator > 3 SV ACS unit for NEOS with 2 indicators

1 SV can be removed upon simple request (common SV for controlling the main actuator and the leak indicator)

- > 1 SV ACS control unit for NEOS with 1 indicator
- > 2 SV ACS control unit for NEOS with 2 indicators

# Single piece plug

Floating PFA seal,

meeting sanitary requirements

perfectly cleanable, ensuring perfect

NO "Normally Open" leak indicator

for detecting a possible leak

leaktightness at high temperature,

resistant to cleaning products

# > Seal profile featuring two sealing points





## NC "Normally Closed" compact pneumatic actuator

- > Easily removable and transformable
- > Common to the full range of DCX shut-off valves
- > Actuator designed for use with the single-action valve
- > Equipped with pneumatic quick-connects to facilitate maintenance

# Leakage collector nozzle

to channel any projections of product in case of diaphragm rupture

### Seal holder plate

common throughout the DCX3 diaphragm shut-off valve range

# **PTFE deformable**

sealing diagram, providing a physical barrier to the outside

## **Connection of the actuator** and shut-off unit

by clamp enabling a rapid maintenance actions

### Thick walled spherical body, machined in the mass

ensuring excellent resistance to expansion stresses > L - T - X configuration

Optional washing microvalve for cleaning the leakage chamber, valve closed









Position of leak indicator on valve can be changed upon request.

OPERATING PRINCIPLE

# **1 LEAK INDICATOR**

# **1 LEAK INDICATOR - 1 CLEANING MICROVALVE**







VALVE CLOSED

Leakage chambe

CIP PHASE VALVE OPEN







**CIP PHASE VALVE OPEN** 

Floating PFA seal PTFE deformable sealing diaphragm

COMPRESSED AIR PASSAGE



PROCESS FLUID PASSAGE

VALVE OPEN



CIP PHASE LEAKAGE CHAMBER VALVE CLOSED



# DIMENSIONS







# DCX3

ØA Tube	В	С	D	ØE	F	G with control unit	ØН	Ι	J	К	L	Weight without c in kg	t of unit ontrol top in Ib
SMS 22.6/25	55	45	110	89	345	480	140	13	198	93	130	4.4	9.70
SMS 35.6/38	70	55	110	89	352	480	140	13	204	93	130	4.6	10.14
SMS 48.5/51	82	70	123	114	381	510	140	19	238	101	138	7.7	16.97
SMS 60.3/63.5	105	85	159	167	430	550	140	26	288	114	151	17.7	39.02
SMS 72.9/76.1	110	95	159	167	436	560	140	26	294	114	151	17.8	39.24
SMS 100/104	130	125	181	217	487	630	140	36	342	128	166	38	83.77
DIN 26/29	55	47	110	89	345	430	140	13	198	93	130	4.4	9.70
DIN 32/35	55	51	110	89	349	430	140	13	201	93	130	4.5	9.92
DIN 38/41	70	55	110	89	351	430	140	13	204	93	130	4.6	10.14
DIN 50/53	80	71	123	114	381	510	140	19	238	101	138	7.7	16.97
DIN 66/70	108	93	159	167	433	550	140	26	291	114	151	17.8	39.24
DIN 81/85	115	105	159	167	440	560	140	26	298	116	153	18.3	40.34
DIN 100/104	130	125	181	217	487	630	140	36	342	128	166	38	83.77

Weight of ACS unit with plastic cover: 1.2 kg

# **OPERATING CONDITIONS**

- Operating temperature: -5 °C to +110 °C (23 °F to 230 °F)
- Sterilisation temperature: Up to 140 °C (284 °F) for 30 min (steam for static mode)
- Delta temperature: 100 °C (212 °F)
- Sealing pressure: 8 bar (116 psi)
- Supply pressure: between 5.5 and 7 bar (between 80 to 101 psi)
- Finish
- Interior: 0.8 μm (180 grit)
  Exterior: 1.2 μm (150 grit)

# Materials

- Indertais
  Body and shut-off unit: stainless steel 1.4404 / AISI 316L
  Actuator: stainless steel 1.4301 / AISI 304
  Plug floating seal PFA
  PTFE deformable sealing diaphragm

# SHUT-OFF VALVE PRESSURE LOSS



ØA Tube	Kv	Air consumption (NI)	ACS unit opening time (s)	ACS unit closing time (s)
SMS 22.6/25	22	0.5	5/10	7/10
SMS 35.6/38	30	0.5	5/10	7/10
SMS 48.5/51	72	1	1	1.5
SMS 60.3/63.5	140	3.5	1.5	3.3
SMS 72.9/76.1	190	3.5	1.5	3.3
SMS 100/104	314	8	2.6	6.5
DIN 26/29	22	0.5	5/10	7/10
DIN 32/35	30	0.5	5/10	7/10
DIN 38/41	30	0.5	5/10	7/10
DIN 50/53	72	1	1	1.5
DIN 66/70	140	3.5	1.5	3.3
DIN 81/85	190	8	1.5	3.3
DIN 100/104	314	8	2.6	6.5

The operating conditions are provided as a guide. Combinations of extreme operating conditions may be inappropriate in certain circumstances. As such, it is highly recommended that you consult our technical service department.



# www.definox.com

# DEFINOX

3 rue des Papetiers ZAC de Tabari Sud 2 - 44190 CLISSON FRANCE Tel: +33 (0)2 28 03 98 50 Fax: +33 (0)2 28 03 88 00 E-mail: info@definox.com

## **DEFINOX** Inc

16720 W. Victor Road - New Berlin 53151 WISCONSIN USA

Tel: +1 262-797-5730 Fax: +1 262-797-5735 E-mail: sales@definox-usa.com

### **DEFINOX** Beijing

Stainless Steel Equipment Ltd No 18 East Road An Ning Zhuang Quinghe Beijing Haidian District BEIJING 100085 CHINA Tel: +86 10-6293-4909 Fax: +86 10-6293-4835

E-mail: msn@definox.com.cn

4ሀርሀዋሏL STዋATEO - RCS B 349728 410 Nantes - 20091 -